



SCAN TO
SHOP

Paolo

OVEN

SPARES DIAGRAM




C
CUPPONE

llk.

PAOLO

table 1






SERVICE AND REPAIRS


From serial number 20093346 / Ovens produced after 08.09.2020

[illegible]

PAOLO
table 2



[illegible]



PAOLO

table 3







TABLE 3

POS.	MODEL	VERSION	CODE	DESCRIPTION			
50	PL435		C01.2385	BLACK MATT THERMOSTAT HANDLE			
51	PL435		C01.2384	SINGLE-PHASE THERMOSTAT 450° C			
52	PL435		C01.2386	PYROMETER D.60			
53	PL435		C01.2400	OVEN 230V LAMP + LENS			
54	PL435		C01.2452	SMALL RED SWITCHING HANDLE			
55	PL435		C01.2453	SWITCH 16A			
56	PL435		C01.2387	GREEN SWITCH 2P			
57	PL435		C01.3153	COOLING FAN			
58	PL435		C01.2556	FAN ACCESSORY			



PAOLO
AC 230
table 4



**70
KIT**





PAOLO
AC 3 N 400
table 6


72
KIT



[illegible]

PAOLO

table 1






SERVICE AND REPAIRS

Up to serial number 20093336 / Ovens produced before 08-09-2020

[illegible]

PAOLO
table 2



[illegible]


**PAOLO**

table 3






TABLE 3

POS.	MODEL	VERSION	CODE	DESCRIPTION			
50	PL435		C01.2385	BLACK MATT THERMOSTAT HANDLE			
51	PL435		C01.2384	SINGLE-PHASE THERMOSTAT 450° C			
52	PL435		C01.2386	PYROMETER D.60			
53	PL435		C01.2400	OVEN 230V LAMP + LENS			
54	PL435		C01.2452	SMALL RED SWITCHING HANDLE			
55	PL435		C01.2453	SWITCH 16A			
56	PL435		C01.2387	GREEN SWITCH 2P			
57	PL435		C01.3153	COOLING FAN			
58	PL435		C01.2556	FAN ACCESSORY			





PAOLO
AC 230
table 4

70
KIT




These components are part of the "COMPLETE WIRING" kit but can also be ordered separately ► see TABLE 3






PAOLO
AC 3 N 400
table 6

72
KIT



These components are part of the "COMPLETE WIRING" kit but can also be ordered separately ► see TABLE 3




[illegible]



PAOLO

SUCTION HOOD

table 1



SERVICE AND REPAIRS

TABLE 1 / TABLE 2							
POS.	MODEL	VERSION	CODE	DESCRIPTION			
1	PL435		C01.2518	FRONT 1040 mm			
2	PL435		C01.2502	LH SHOULDER			
3	PL435		C01.2503	RH SHOULDER			
4	PL435		C01.2520	HOOD EXTERNAL FILTER			
5	PL435		C01.2522	HOOD INTERNAL FILTER			
6	PL435		C01.2508	FEM-FEM TUBE 80x505 316L BA			
7	PL435		C01.2510	MALE-FEM CURVE 80-90 316L BA			
8	PL435		C01.2511	STAINLESS STEEL HANDLE FOR HOOD FILTERS			
9	PL435		C01.2512	FAN PROTECTION GRILLE			
10	PL435		C01.2513	HOOD CONTROL BOARD			
11	PL435		C01.2514	ASPIRATOR VT150			
12	PL435		C01.2515	HOOD POLYCARBONATE FRONT AS CP			
13	PL435		C01.2516	HOOD POLYCARBONATE FRONT NT CP			
14	PL435		C01.2517	TERMINAL 450V 32A 2 INPUTS			